

PM867K02

Compact Product Suite hardware selector



The CPU board contains the microprocessor and RAM memory, a real-time clock, LED indicators, INIT push button, and a CompactFlash interface.

The base plate of the PM867 controller has two RJ45 Ethernet ports (CN1, CN2) for connection to the Control Network, and two RJ45 serial ports (COM3, COM4). One of the serial ports (COM3) is an RS-232C port with modem control signals, whereas the other port (COM4) is isolated and used for the connection of a configuration tool. The controller supports CPU redundancy for higher availability (CPU, CEX-Bus, communication interfaces and S800 I/O).

The high integrity functionality is enabled by the addition of an SM812 module and the SIL-certified software. The AC 800M High-Integrity also offers IEC 61508 and TÜV-certified control environment for combining safety and business-critical process control in one controller unit without sacrificing the safety integrity. Only compatible for 800xA 6.0.2 and onwards. Please see Product Update for more information.

Package including:

- 2 pcs PM867, CPU
- 2 pcs TP830, Baseplate, width = 115mm
- 2 pcs TB807, ModuleBus terminator
- 1 pcs TK850, CEX-bus expansion cable
- 1 pcs TK851, RCU-Link cable
- 2 pcs Battery for memory backup (4943013-6) 1 for each CPU

Features and benefits

- ISA Secure certified - [Read more](#)
- AC 800M High up to SIL 3 certified using PM865/SM811 or PM867/SM812
- Supports S800 I/O High Integrity (PM865, PM866A, PM867 and PM891)
- The controller can be configured with 800xA control builder
- The controller has full EMC certification
- TÜV Certified SIL 2 and SIL 3
- Built-in redundant Ethernet Communication ports

| General info | |
|--------------------------------------|-------------------------|
| Article number | 3BSE081638R1 (PM867K02) |
| Redundancy | Yes |
| High Integrity | Yes |
| Clock Frequency | 133 MHz |
| Performance, 1000 boolean operations | 0.09 ms |
| Performance | 0.09 ms |
| Memory | 64 MB |
| RAM available for application | 46.559 MB |
| Flash memory for storage | No |

| Detailed data | |
|---|---|
| Processor type | MPC866 |
| Switch over time in red. conf. | Max 10 ms |
| No. of applications per controller | 32 |
| No. of programs per application | 64 |
| No. of diagrams per application | 128 |
| No. of tasks per controller | 32 |
| Number of different cycle times | 32 |
| Cycle time per application programs | Down to 1 ms |
| Flash PROM for firmware storage | 18 MB |
| Power supply | 24 V DC (19.2-30 V DC) |
| Power consumption +24 V typ/max | 210 / 360 mA |
| Power dissipation | 5.1 W (8.6 W max) |
| Redundant power supply status input | Yes |
| Built-in back-up battery | Lithium, 3.6 V |
| Clock synchronization | 1 ms between AC 800M controllers by CNCP protocol |
| Event queue in controller per OPC client | Up to 3000 events |
| AC 800M transm. speed to OPC server | 36-86 events/sec, 113-143 data messages/sec |
| Comm. modules on CEX bus | 12 |
| Supply current on CEX bus | Max 2.4 A |
| I/O clusters on Modulebus with non-red. CPU | 1 electrical, 7 optical |
| I/O clusters on Modulebus with red. CPU | 0 electrical + 7 optical |
| I/O capacity on Modulebus | Max 96 (single PM867) or 84 (red. PM867) I/O modules |
| Modulebus scan rate | 0 - 100 ms (actual time depending on number of I/O modules) |
| Supply current on Electrical Modulebus | 24 V : max 1.0 A 5 V : max 1.5 A |
| Ethernet channels | 2 |
| Ethernet interface | Ethernet (IEEE 802.3), 10 Mbit/s, RJ-45, female (8-pole) |
| Control Network protocol | MMS (Manufacturing Message Service) and IAC (Inter Application Communication) |
| Recommended Control Network backbone | 100 Mbit/s switched Ethernet |
| Real-time clock stability | 100 ppm (approx. 1 h/year) |
| RS-232C interface | 2 (one general, 1 for service tool) |
| RS-232C interface (COM3) (non red. only) | RS-232C, 75-19 200 baud, RJ-45 female (8-pole), not opto isolated, full RTS-CTS support |
| RS-232C interface (COM4) (non red. only) | RS-232C, 9 600 baud, RJ-45 female (8-pole), opto isolated, no RTS-CTS support |

| Environment and certification | |
|--------------------------------------|--|
| Temperature, Operating | +5 to +55 °C (+41 to +131 °F) |
| Temperature, Storage | -40 to +70 °C (-40 to +158 °F) |
| Temperature changes | 3 °C/minutes according to IEC/EN 61131-2 |
| Pollution degree | Degree 2 according to IEC/EN 61131-2 |
| Corrosion protection | G3 compliant to ISA 71.04 |
| Relative humidity | 5 to 95 %, non-condensing |
| Emitted noise | < 55 dB (A) |
| Vibration | 10 < f < 50 Hz: 0.0375 mm amplitude, 50 < f < 150 Hz: 0.5 g acceleration, 5 < f < 500 Hz: 0.2 g acceleration |
| Rated Isolation Voltage | 500 V a.c. |
| Dielectric test voltage | 50 V |
| Protection class | IP20 according to EN 60529, IEC 529 |
| Altitude | 2000 m (6 562 ft) according to IEC/EN 61131-2 |
| Emission & Immunity | EN 61000-6-4, EN 61000-6-2 |
| Environmental conditions | Industrial |
| CE Mark | Yes |
| Electrical Safety | EN 50178, IEC 61131-2, UL 61010-1, UL 61010-2-201 |
| Hazardous location | UL 60079-15, cULus Class 1, Zone 2, AEx nA IIC T4, ExnA IIC T4Gc X |
| ISA Secure certified | Yes |
| Marine certificates | ABS, BV, DNV-GL (LR, Lloyd (Pending)) |
| TUV Approval | Yes |
| RoHS compliance | EN 50581:2012 |
| WEEE compliance | DIRECTIVE/2012/19/EU |

| Dimensions | |
|-------------------------|--|
| Width | 119 mm (4.7 in.) |
| Height | 186 mm (7.3 in.) |
| Depth | 135 mm (5.3 in.) |
| Weight (including base) | K01 1200 g (2.6 lbs) / K02 2700 g (5.95 lbs) |

—
solutions.abb/compactproductsuite
solutions.abb/controlsystems

—
We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved