

# TU866

## Compact Product Suite hardware selector



### TU866 MTU for Ethernet FCI and S100 I/O




The TU866 is an Ethernet Fieldbus Communication Interface Module Termination Unit (MTU) hosting single/redundant Ethernet FCI Communications Interface Modules (CI846) and single/redundant Ethernet Adapters (TC810, TC811) for reliable communications with the AC 800M controllers. The TU866 also hosts single/redundant S100 I/O connectors for S100 I/O modules.

Please observe this item can not be ordered separately.

## Features and benefits

- Two mounting slots for connecting single/redundant CI846 FCI modules
- Two mounting slots for connecting single/redundant Ethernet Adapters
- Two connectors for connecting single/redundant 24 V power supplies
- Two S100 communication connectors for connecting S100 I/O subbracks using standard cables which connect between the FCI and the bus extender modules
- Mountable on a 35 mm DIN Rail

# More info



General info	
Article number	2PAA125749R1
Communication protocol	Ethernet
Type	MTU for Ethernet FCI (S100 I/O)
Master or slave	Slave
High integrity	N/A
Intrinsic safety	N/A
Mounting	DIN Rail (vertical mounting)

---

**Environment and certification**

Temperature, Operating	-5 °C (23 °F) to +55 °C (131 °F)
Temperature, Storage	-5 °C (23 °F) to +55 °C (131 °F)
Pollution degree	Pollution Degree 2 acc. to IEC 60664-1
Relative humidity	5 to 95 %, non-condensation
Altitude	-1000 to 2000 m
Mechanical operating conditions	IEC 61131-2
EMC	IEC/EN 61000-6-4, IEC/EN 61000-6-2
Overvoltage categories	Category II acc. to IEC 60664-1
Equipment class	Class III acc. to IEC/EN 61010-2-201
Ingress protection	IP20 acc. to IEC 60529
CE-marking	Yes
UKCA	Yes
Electrical Safety	IEC/EN 61010-1 UL 61010-1 CSA-C22.2 No. 61010-1-12 IEC/EN 61010-2-201 UL 61010-2-201 CSA C22.2 No. 61010-2-201
Corrosive atmosphere	G3
RoHS compliance	Yes
WEEE compliance	EU

---

**Dimensions**

Width	135 mm
Depth	210 mm
Height	95.5 mm
Weight (including base)	605 g

---

—  
**[solutions.abb/compactproductsuite](https://solutions.abb/compactproductsuite)**  
**[solutions.abb/controlsystems](https://solutions.abb/controlsystems)**

—  
We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved