

# DI802

## Compact Product Suite hardware selector



The DI802 is an 8 channel 120 V a.c./d.c. digital input module for the S800 I/O. This module has 8 digital inputs. The a.c. input voltage range is 77 - 130 volt and the input current is 10 mA at 120 V a.c. The d.c. input range is 75 - 145 V and the input current is 2.8 mA at 110 V. The inputs are individually isolated. Every input channel consists of current limiting components, EMC protection components, input state indication LED and optical isolation barrier.

### Features and benefits

- 8 channels for 120 V a.c./d.c. inputs with current sinking
- Individually isolated channels
- Voltage supervision of field input power
- Input status indicators
- Signal filtering
- Process connection via detachable connectors

General info	
Article number	3BSE022360R1
Type	Digital Input
Signal specification	120 V a.c., 110 V d.c.
Number of channels	8
Signal type	Current sinking
HART	No
SOE	No
Redundancy	No
High integrity	No
Intrinsic safety	No
Mechanics	S800L

Detailed data	
Input voltage range, "0"	0..30 V a.c., 0..20 V d.c.
Input voltage range, "1"	77..130 V a.c., 75..145 V d.c.
Input impedance	12 kΩ (a.c.) 39 kΩ (d.c.)
Isolation	Individually isolated channels
Filter times (digital, selectable)	2, 4, 8, 16 ms
Input frequency range	47..63 Hz
Analog filter On/Off delay	5 / 18 ms
Maximum field cable length	200 meters (219 yards) 100 pF/m for a.c., 600 meters (656 yards) for d.c.
Rated insulation voltage	250 V
Dielectric test voltage	2000 V a.c.
Power dissipation	Typ. 2.8 W
Current consumption +5 V Modulebus	50 mA
Current consumption +24 V Modulebus	0
Current consumption +24 V external	0
Supported wire size	Solid: 0.05-2.5 mm², 30-12 AWG
	Stranded: 0.05-1.5 mm², 30-12 AWG
	Recommended torque: 0.5-0.6 Nm
	Stripping length 6-7.5mm, 0.24-0.30 inch

Diagnostics	
Front LED's	S(tatus) (run or fault), Channel 1-16 ("0" or "1")
Supervision	Process voltage supervision on channel 8
Status indication of supervision	Module Error, Module Warning, Channel Error

Environment and certification	
CE mark	Yes
Electrical safety	EN 61010-1, UL 61010-1, EN 61010-2-201, UL 61010-2-201
Hazardous Location	-
Marine certification	ABS, BV, DNV, LR
Temperature, Operating	0 to +55 °C (+32 to +131 °F), approvals are issued for +5 to +55 °C
Temperature, Storage	-40 to +70 °C (-40 to +158 °F)
Pollution degree	Degree 2, IEC 60664-1
Corrosion protection	ISA-S71.04: G3
Relative humidity	5 to 95 %, non-condensing
Max ambient temperature	55 °C (131 °F), for vertical mounting 40 °C (104 °F)
Protection class	IP20 according to IEC 60529
Mechanical operating conditions	IEC/EN 61131-2
EMC	EN 61000-6-4 and EN 61000-6-2
Overvoltage categories	IEC/EN 60664-1, EN 50178
Equipment class	Class I according to IEC 61140; (earth protected)
RoHS compliance	DIRECTIVE/2011/65/EU (EN 50581:2012)
WEEE compliance	DIRECTIVE/2012/19/EU

Dimensions	
Width	86.1 mm (3.4")
Depth	58.5 mm (2.3")
Height	110 mm (4.33")
Weight	0.24 kg (0.53 lbs.)

---

**[solutions.abb/compactproductsuite](https://solutions.abb/compactproductsuite)  
[solutions.abb/controlsystems](https://solutions.abb/controlsystems)**

---

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved