

TL830/TL831

Compact Product Suite hardware selector



Select I/O is an Ethernet networked, single channel granular I/O system for the ABB Ability™ System 800xA automation platform. Select I/O helps decouple project tasks, minimizes the impact of late changes and supports standardization of I/O cabinetry ensuring automation projects are delivered on-time and under budget. A Signal Conditioning Module (SCM) performs the necessary signal conditioning and powering of the connected field device for one I/O channel.

TL830 and TL831 IP30 protection cover for power inlets on FCI base plate TU865/TU860. 20 pieces of TL830 and 10 pieces of TL831 per package.

Features and benefits

- Protection cover for power inlets on FCI base plate TU865/TU860
- Usable for enabling IP30 for the power supply connectors
- Required in case that intrinsically safe Select I/O equipment is used together with an FCI in the same cabinet
- TL830 has to be used to cover the power supply connector with any connected power supply cables
- TL831 has to be used to cover the power supply connectors without connected power supply cables

General info

| | |
|------------------|--------------|
| Article number | 3BSE093013R1 |
| Type | IP30 Cover |
| Intrinsic safety | Yes |
| Mechanics | Select I/O |

| Environment and certification | |
|--------------------------------------|--|
| Temperature, Operating | -40°C (-40°F) to +70°C (158°F) |
| Temperature, Storage | -40°C (-40°F) to +85°C (185°F) |
| Pollution degree | Pollution Degree 2 acc. to IEC 60664-1 |
| Relative humidity | 5 to 95 % no condensation |
| Altitude | -1000 to 3000 m, (-100 ... 2000 m for Zone 2/Class I Div 2) |
| Mechanical operating conditions | IEC 61131-2 |
| EMC | IEC/EN 61000-6-4, IEC/EN 61000-6-2 |
| Overvoltage categories | Category II, IEC 60664-1 |
| Protection class | IP20 according to IEC 60529 |
| CE-marking | Yes |
| Electrical Safety | IEC/EN 61010-1, IEC 61010-2-201, UL 61010-2-201, CSA C22.2 No. 61010-2-201 |
| Hazardous Area | EN 60079-0, EN60079-7 |
| Marine certification | ABS |
| Corrosive atmosphere | G3 (ISA-S71.04) |
| RoHS compliance | DIRECTIVE/2011/65/EU (EN 50581:2012) |
| WEEE compliance | DIRECTIVE/2012/19/EU |

| Dimensions | |
|-------------------------|--|
| Width | 32 mm (1.25 in.) |
| Depth | 20.8 mm (0.81 in.) |
| Height | 20 mm (0.78 in.) |
| Weight (including base) | TL830 2.5 g (0.005 lbs), TL831 2.7 g (0.006 lbs) |

—
solutions.abb/compactproductsuite
solutions.abb/controlsystems

—
We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2026 ABB All rights reserved