

# FTB890K01

## Compact Product Suite hardware selector



Select I/O is an Ethernet networked, single channel granular I/O system for the ABB Ability™ System 800xA automation platform. Select I/O helps decouple project tasks, minimizes the impact of late changes and supports standardization of I/O cabinetry ensuring automation projects are delivered on-time and under budget.

The FTB890 is a field terminal block with 4 screw terminals to be used with a single intrinsically safe Signal Conditioning Module. The FTB is installed on the MTU for Select I/O (TUS810) and includes a keying mechanism that is set to a certain code when an SCM is inserted for the first time to ensure only the same type of SCM can be installed in that slot. The key can be reset by removing and reinserting the FTB. (10 pieces per package).

### Features and benefits

- One slot for connection of SCM
- Four screw terminals for connection of wires
- Coding system with 5 coding fingers for self-learning and resettable coding of the SCM type
- Can be used in hazardous areas
- Hole for each terminal for connecting test probes (for measurements)

General info	
Article number	3BSE078760R1
Type	Field Terminal Block IS
Redundancy	No
Intrinsic safety	Yes
Mechanics	Select I/O

Detailed data	
Installation in Hazardous Area/Locations	Yes/Yes

<b>Environment and certification</b>	
Temperature, Operating	-40°C (-40°F) to +70°C (158°F)
Temperature, Storage	-40°C (-40°F) to +85°C (185°F)
Pollution degree	Pollution Degree 2 acc. to IEC 60664-1
Relative humidity	5 to 95 %, non-condensation
Altitude	-1000 to 5000 m (restrictions apply)
Mechanical operating conditions	IEC 61131-2
EMC	IEC/EN 61000-6-4, IEC/EN 61000-6-2
Overvoltage categories	Category II acc. to IEC 60664-1
Protection class	IP20 acc. to IEC 60529
CE-marking	Yes
UKCA	Yes
Electrical Safety	IEC/EN 61010-1 UL 61010-1 CSA-C22.2 No. 61010-1-12 IEC/EN 61010-2-201 UL 61010-2-201 CSA C22.2 No. 61010-2-201
Marine certification	DNV, ABS
Corrosive atmosphere	G3
RoHS compliance	EU RoHS, UAE RoHS, CN RoHS
WEEE compliance	EU
Hazardous Area ATEX	Simple Apparatus acc. to IEC/EN 60079-11 clause 5.7
Hazardous Area IECEx	Simple Apparatus acc. to IEC/EN 60079-11 clause 5.7
Hazardous Location US/CAN	cULus CL I, ZN 2, AEx ec IIC T4 Gc, Ex ec IIC T4 Gc X CL I, ZN 2, AEx nA IIC T4 Gc, Ex nA IIC T4 Gc X CL I, DIV 2, Groups A-D T4
Hazardous Area CCC	Simple Apparatus acc. to IEC/EN 60079-11 clause 5.7

<b>Dimensions</b>	
Width	10 mm (0.39 in.)
Depth	85.2 mm (3.35 in.)
Height	74.8 mm (2.94 in.)
Weight (including base)	40 g (0.08 lbs)

—  
[solutions.abb/compactproductsuite](https://solutions.abb/compactproductsuite)  
[solutions.abb/controlsystems](https://solutions.abb/controlsystems)

—  
We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2026 ABB All rights reserved