

BC820K02

Compact Product Suite hardware selector



The CEX-Bus unit BC820 is used for extending the onboard communication ports with communication interface units. It is also possible to use redundant communication interfaces on the CEX-Bus. The BC820 CEX-Bus Interconnection Unit offers a way to section the CEX-Bus into two independent segments up to 200 meters apart. This improves availability in systems with redundant communication interfaces.

The BC820 can be used with PM858, PM862, PM866 (PR.F or later, which corresponds to PR.H or later for PM866K01), and PM866A.

The BC820 is powered from the processor unit via the CEX-Bus and can also support the CEX-Bus with redundant power through its external connector for power supply. BC820 transmits the RCU-Link and extends the CEX-Bus and RCU-Link cable length up to 200 m. The number of CEX-Bus interfaces is limited to 6 with each BC820.

You need to provide the following cables at a suitable length (not included in the BC820K02 kit):

RCU Control Link: Modular Jack, RJ45, shielded twisted pair crossover cable with all four pairs crossed: EIA/TIA-568 standard crossover T568A to T568B. Length: max 200m.

RCU Data Link: The optical interconnection is compatible with LC Duplex optical connector interface conforming to ANSI TIA/EIA60-10 (FOCIS 10A). The type of optical cable is 50/125µm OM3 fiber. Length: max 200m.

For more information about the cables see 3BSE036351-*

Features and benefits

- Supports redundant communication interface units.
- Supports on-line replacement of the CPU.
- External power supply.
- Supports hot swap.

More info

The BC820K02 kit includes:

- BC820, RCU-Link and CEX-Bus Interconnection Unit, 2 units
- TP850, Baseplate, width=60mm, 2 units
- TK857 RCU-Link Cable for BC820, 2 units. Length = 0.3 m
- TB850, CEX-Bus Terminator, 2 units

General info

Article number	3BSE071500R1 (BC820K02)
Redundancy	Yes
High Integrity	No
Performance	Hot swap supported

Detailed data

Power supply	Inputs designated L+ and L- 24 V nominal, variation between 19.2 V DC and 30 V DC.
Power consumption +24 V typ/max	120 mA typical (200 mA max)
Power dissipation	2.9 W typical

Environment and certification

Temperature, Operating	+5 to +55 °C (+41 to +131 °F)
Temperature, Storage	-40 to +70 °C (-40 to +158 °F)
Relative humidity	5 to 95 %, non-condensing
Protection class	IP20 according to EN 60529, IEC 529
CE Mark	Yes
Electrical Safety	UL 61010-1, UL 61010-2-201
Hazardous location	cULus Class 1, Zone 2, AEx nA IIC T4, ExnA IIC T4Gc X
Marine certificates	ABS, BV, DNV-GL, LR
RoHS compliance	EN 50581:2012
WEEE compliance	DIRECTIVE/2012/19/EU

Dimensions

Width	59 mm (2.9 in.)
Height	185 mm (7.3 in.)
Depth	127.5 mm (5.0 in.)
Weight (including base)	1.4 kg (3.1 lbs) (BC820K02 package)

—
solutions.abb/compactproductsuite
solutions.abb/controlsystems

—
We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved