

DATA SHEET

CI801

Compact Product Suite hardware selector



S800 I/O is a comprehensive, distributed and modular process I/O system that communicates with parent controllers and PLCs over industry-standard field buses. The CI801 Fieldbus Communication Interface (FCI) module is a configurable communication interface that performs operations such as signal processing, gathering of supervision information, OSP handling, Hot Configuration InRun, HART pass-trough and configuration of I/O modules. The FCI connects to the controller through of the PROFIBUS-DPV1 fieldbus.

Features and benefits

- PROFIBUS DP PROFIBUS-DPV1 fieldbus interface.
- Supervisory functions of I/O ModuleBus
- Isolated power supply to I/O modules
- OSP handling and configuration
- Input power fused
- Hot Configuration In Run
- HART pass-through

General info

Article number	3BSE022366R1
Communication protocol	PROFIBUS DP-V1
Master or slave	Slave
Line redundancy	No
Module redundancy	No
Hot Swap	No
Used together with HI Controller	Yes

Detailed data

24 V consumption typ.	140 mA
-----------------------	--------

Environment and certification

CE- marking	Yes
Electrical Safety	EN 61010-1, UL 61010-1, EN 61010-2-201, UL 61010-2-201
Hazardous location	C1 Div 2 cULus, C1 Zone 2 cULus, ATEX Zone 2
Marine certificates	ABS, BV, DNV-GL, LR
Temperature, Operating	0 to +55 °C (+32 to +131 °F), approvals are issued for +5 to +55 °C
Temperature, Storage	-40 to +70 °C (-40 to +158 °F)
Pollution degree	Degree 2, IEC 60664-1
Corrosion protection	ISA-S71.04: G3
Relative humidity	5 to 95 %, non-condensing
Max ambient temperature	55 °C (131 °F), for vertical mounting 40 °C (104 °F)
Protection class	IP20 according to EN60529, IEC 529
RoHS compliance	EU RoHS, UAE RoHS, CN RoHS
WEEE compliance	DIRECTIVE/2012/19/EU

Dimensions

Width	85.8 mm (3.38 in.)
Height	136 mm (5.35 in.) including latch
Depth	58.5 mm (2.30 in.)
Weight	0.3 kg (0.66 lbs.)

solutions.abb/compactproductsuite
solutions.abb/controlsystems

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2026 ABB All rights reserved