

DATA SHEET

CI873A

Compact Product Suite hardware selector



The CI873A is an AC 800M communication interface that connects to external Ethernet devices using the EtherNet/IP protocol. The TP867 Baseplate has two RJ45 Ethernet connectors, but only the CH1 connector that supports 100Mbps is used. The CI873 expansion unit contains the CEX-Bus logic, a communication unit, and a DC/DC converter that supplies the required voltage from +24 V supply through the CEX-Bus.

The CI873A module will only work with System 800xA 6.0.3.3, 6.1.1 and subsequent versions. The CI873A support 6 redundant pairs of CI873A from $5.1\,\text{FP4}$.

Features and benefits

- Supports Ethernet/IP and Device Net protocols
- Support 6 redundant pairs of CI873A from 5.1 FP4

General info		
Article number	3BSE092695R1	
Communication protocol	EtherNet IP / DeviceNet	
Master or slave	Master	
Transmission speed	10/100 Mbit/s	
Line redundancy	No	
Module redundancy	Yes	
Hot Swap	Yes	
Used together with HI Controller	Yes	

Detailed data		
Max units on CEX bus	12	
Connector	RJ-45 female (8-pin)	
24 V consumption typ.	typ 160 mA	

Environment and certification		
Temperature, Operating	0 to +55 °C (+32 to +131 °F)	
Temperature, Storage	-40 to +70 °C (-40 to +158 °F)	
Altitude	2000 m according to IEC/EN 61131-2	
Pollution degree	Degree 2 according to IEC/EN 61131-2	
Corrosion protection	G3 compliant to ISA 71.04	
Relative humidity	5 to 95 %, non-condensing	
Protection class	IP20 according to EN60529, IEC 529	
CE- marking	Yes	
Electrical Safety	UL 61010-1, UL 61010-2-201	
Hazardous location	UL 60079-15, cULus Class 1, Zone 2, AEx nA IIC T4, ExnA IIC T4Gc X	
Marine certificates	DNV-GL, (Pending: ABS, BV, LR)	
RoHS compliance	DIRECTIVE/2011/65/EU (EN 50581:2012)	
WEEE compliance	DIRECTIVE/2012/19/EU	

Dimensions		
Width	59 mm (2.3 in.)	
Height	185 mm (7.3 in.)	
Depth	127.5 mm (5.0 in.)	
Weight (including base)	700 g (1.5 lbs)	



solutions.abb/compactproductsuite solutions.abb/controlsystems

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved