

# TU844

## Compact Product Suite hardware selector



The TU844 MTU can have up to 8 I/O channels and 2+2 process voltage connections. Each channel has two I/O connections and one ZP connection. Input signals are connected via individual shunt sticks, TY801. The shunt stick is used to choose between voltage and current input. The maximum rated voltage is 50 V and maximum rated current is 2 A per channel.

The MTU distributes the two ModuleBuses, one to each I/O module and to the next MTU. It also generates the correct address to the I/O modules by shifting the outgoing position signals to the next MTU.

The MTU can be mounted on a standard DIN rail. It has a mechanical latch that locks the MTU to the DIN rail. Four mechanical keys, two for each I/O module, are used to configure the MTU for different types of I/O modules. This is only a mechanical configuration and it does not affect the functionality of the MTU or the I/O module. Each key has six positions, which gives a total number of 36 different configurations.

### Features and benefits

- Complete installation of I/O modules using 2-wire connections and field power distribution.
- Up to 8 channels of field signals and process power connections.
- Connections to two ModuleBuses and I/O modules.
- Mechanical keying prevents insertion of the wrong I/O module.
- Latching device to DIN rail for grounding.
- DIN rail mounting.

General info	
Article number	3BSE021445R1
Type	Redundant
Connection	Terminal block
Channels	8
Voltage	50 V
Mounting	Horizontal
Mounting detail	55 ° (131 °F)
Use with I/O	AI845, AI880, AI880A and DP840
Process connections	40 up to 8 I/O channels (2 terminals per channel) 4 Process power 20 Process power (0 V)
Single/redundant I/O	Redundant

<b>Detailed data</b>	
Maximum current per I/O channel	2 A
Maximum current process connection	5 A
Acceptable wire sizes	Solid: 0.2 - 4 mm <sup>2</sup> Stranded: 0.2 - 2.5 mm <sup>2</sup> , 24 - 12 AWG Recommended torque: 0.5 - 0.6 Nm Stripping length: 7 mm
Dielectric test voltage	500 V a.c.

<b>Environment and certification</b>	
CE mark	Yes
Electrical safety	EN 61010-1, UL 61010-1, EN 61010-2-201, UL 61010-2-201
Hazardous Location	C1 Div 2 cULus, C1 Zone 2 cULus, ATEX Zone 2
Marine certification	ABS, BV, DNV-GL, LR
Temperature, Operating	0 to +55 °C (+32 to +131 °F), approvals are issued for +5 to +55 °C
Temperature, Storage	-40 to +70 °C (-40 to +158 °F)
Pollution degree	Degree 2, IEC 60664-1
Corrosion protection	ISA-S71.04: G3
Relative humidity	5 to 95 %, non-condensing
Max ambient temperature	55 °C (131 °F)
Protection class	IP20 according to IEC 60529
Mechanical operating conditions	IEC/EN 61131-2
EMC	EN 61000-6-4, EN 61000-6-2
Overvoltage categories	IEC/EN 60664-1, EN 50178
Equipment class	Class I according to IEC 61140; (earth protected)
RoHS compliance	EN 50581:2012
WEEE compliance	DIRECTIVE/2012/19/EU

<b>Dimensions</b>	
Width	131 mm (5.16") including connector, 124 mm (4.88") edge to edge installed
Depth	64 mm (2.52") including terminals
Height	186.5 mm (7.34") including locking device
Weight	0.6 kg (1.3 lbs.)

—  
[solutions.abb/compactproductsuite](https://solutions.abb/compactproductsuite)  
[solutions.abb/controlsystems](https://solutions.abb/controlsystems)

—  
We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved