

# TL814K01

## Compact Product Suite hardware selector

Select I/O is an Ethernet networked, single channel granular I/O system for the ABB Ability™ System 800xA automation platform. Select I/O helps decouple project tasks, minimizes the impact of late changes and supports standardization of I/O cabinetry ensuring automation projects are delivered on-time and under budget. A Signal Conditioning Module (SCM) performs the necessary signal conditioning and powering of the connected field device for one I/O channel.

Empty slot protector for a High Integrity Module slot on the Ethernet FCI Module Termination Unit. 10 pieces per package.



### Features and benefits

- Empty slot protector for a High Integrity Module slot on the Ethernet FCI Module Termination Unit
- Included with every TU860 and TU865

General info	
Article number	3BSE088174R1
Type	Empty slot protector HI Module
Hot swap	Yes
Mechanics	Select I/O

## Environment and certification

Temperature, Operating	-40°C (-40°F) to +70°C (158°F)
Temperature, Storage	-40°C (-40°F) to +85°C (185°F)
Pollution degree	Pollution Degree 2 acc. to IEC 60664-1
Relative humidity	5 to 95 % no condensation
Altitude	-1000 to 3000 m, (-100 ... 2000 m for Zone 2/Class I Div 2)
Mechanical operating conditions	IEC 61131-2
EMC	IEC/EN 61000-6-4, IEC/EN 61000-6-2
Overvoltage categories	Category II, IEC 60664-1
Protection class	IP20 according to IEC 60529
CE-marking	Yes
Electrical Safety	IEC/EN 61010-1, IEC 61010-2-201, UL 61010-2-201, CSA C22.2 No. 61010-2-201
Hazardous Area	EN 60079-0, EN60079-7, EN60079-15, UL 12.12.01 / CSA C22.2 No. 213-17
Marine certification	ABS
Corrosive atmosphere	G3 (ISA-S71.04)
RoHS compliance	DIRECTIVE/2011/65/EU (EN 50581:2012)
WEEE compliance	DIRECTIVE/2012/19/EU

## Dimensions

Width	72 mm (2.83 in.)
Depth	50.5 mm (1.99 in.)
Height	19.8 mm (0.78 in.)
Weight (including base)	16.8 g (0.03 lbs)

—  
**[solutions.abb/compactproductsuite](https://solutions.abb/compactproductsuite)**  
**[solutions.abb/controlsystems](https://solutions.abb/controlsystems)**

—  
We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2024 ABB All rights reserved